



YTS451RT, ACSR - Full Tension Compression Splice



By Burndy
Catalog # [YTS451RT](#)

Al Sleeve for Full tension Splice Kit, Length: 28.96 IN, Die Index:
725

Features

- ACSR Full Tension Compression Splice
- High Temperature

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	• 715.5 (26/7) Starling Kcmil • 715.5 (54/7) Crow Kcmil • 795 (24/7) Cuckoo Kcmil • 795 (26/7) Drake Kcmil • 795 (45/7) Tern Kcmil • 795 (54/7) Condor Kcmil
---------------------------	--

Configuration

Connector Type	Splice
Dimensions	
Dimension - L Length Overall mm	28.96 mm
Dimension - Length Overall inch	735.6 in
General	
Trade Name	HYSPLICE™
UPC	781810016503
Material	Aluminum
UPC 12 Digit	781810016503
UPC 14 Digit GTIN	00781810016503

Logistics

Minimum Pack Quantity	1
Pallet Quantity	280
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)