



YTS451RT48RS, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS451RT48RS](#)

Drake ACSR Splice



Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	• 715.5 (26/7) Starling kcmil • 715.5 (30/19) Redwing kcmil • 795 (54/7) Condor kcmil • 795 (26/7) Drake kcmil
Conductor - ACSR Str Size Range	715.5 (26/7) Starling kcmil-795 (26/7) Drake kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	736 mm
Dimension - Outside Diameter	1.80 in
Dimension - Length Overall	28.96 in

General

Trade Name	HYSPLICE™
UPC	781810211144
Material	Aluminum
UPC 12 Digit	781810211144
UPC 14 Digit GTIN	00781810211144

Logistics

Minimum Pack Quantity	1
Pallet Quantity	210
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)