



YTS457A, Aluminum Full Tension Splice

By Burndy
Catalog # [YTS457A](#)

Aluminum Full Tension HYSPLICE™, 1351.5-1431 Kcmil, 728 Index



Features

- Aluminum Compression Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1351.5 (61) Kcmil 1431 (61) Kcmil
-------------------------	---

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	507 mm
mm	
Dimension - Length Overall	19.96 in
inch	

General

Trade Name	HYSPLICE™
Die Index	728
UPC	781810183083
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810183083
UPC 14 Digit GTIN	00781810183083

Logistics

Minimum Pack Quantity	1
Pallet Quantity	288
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)