



YTS463A, Aluminum Full Tension Splice

By Burndy
Catalog # [YTS463A](#)

Aluminum tube full tension splice for stranded aluminum transmission line, 1590 Kcmil, 728 Index



Features

- Aluminum Compression Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1590 (61) Kcmil
-------------------------	-----------------

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	546 mm
------------------------------	--------

Dimension - Length Overall	21.50 in
----------------------------	----------

General

Plated	N
Trade Name	HYSPLICE™
Die Index	728
UPC	781810263013
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810263013
UPC 14 Digit GTIN	00781810263013

Logistics

Minimum Pack Quantity	1
Pallet Quantity	288
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)