



YTS481RS, ACSR - Full Tension Compression Splice



By Burndy
Catalog # [YTS481RS](#)

Steel Sleeve, 795, 900, 954 kcmil ACSR, 230 V, 9.00" L, 726
Index, Included in Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	795 (45/7) Tern 900 (45/7) Ruddy Kcmil 954 (45/7) Rail Kcmil
---------------------------	--

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - Length Overall	9.00
inch	

General

Trade Name	HYSPLICE™
Die Index	726
UPC	781810016305
Material	Aluminum
UPC 12 Digit	781810016305
UPC 14 Digit GTIN	00781810016305

Logistics

Minimum Pack Quantity	1
Pallet Quantity	900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)