



YTS48R, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS48R](#)



Al Sleeve, 795, 900, 954 kcmil ACSR, 230 V, 29.16" L, 727 Index,
Included in Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	795 (30/19) Mallard Kcmil 900 (45/7) Rubby 954 (45/7) Rail Kcmil 954 (54/7) Cardinal Kcmil
---------------------------	--

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall mm	740.7 mm
Dimension - Length Overall inch	29.16 in

General

Trade Name	HYSPLICE™
Die Index	727
UPC	781810016275
Material	Aluminum
UPC 12 Digit	781810016275
UPC 14 Digit GTIN	00781810016275

Logistics

Minimum Pack Quantity	1
Pallet Quantity	210
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)