



YTS48R481RSHT, High Temperature Splice

By Burndy
Catalog # [YTS48R481RSHT](#)



Compression High Temperature Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSS Str Size Range	954 (45/7) kcmil
Conductor - ACSS Str Size	954 (45/7) kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
----------------	----------

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	4.19 in
Dimension - Outside Diameter inch	1.97 in
Dimension - Length Overall inch	36.00 in

General

Trade Name	HYSPLICE™
UPC	781810510995
UPC 12 Digit	781810510995
UPC 14 Digit GTIN	00781810510995

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)