



YTS48R48RS, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS48R48RS](#)



Two piece full tension splice kit, 954 Kcmil, 727 Index, Kit includes both Steel and aluminum sleeves

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	954 (54/7) Cardinal kcmil
Conductor - ACSR Str Size Range	954 (54/7) Cardinal kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall mm	741 mm
---------------------------------	--------

Dimension - B Length inch	4.00 in
Dimension - Outside Diameter inch	1.97 in
Dimension - Length Overall inch	29.16 in

General

Trade Name	HYSPLICE™
UPC	781810097021
Material	Aluminum
UPC 12 Digit	781810097021
UPC 14 Digit GTIN	00781810097021

Logistics

Minimum Pack Quantity	1
Pallet Quantity	175
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)