



YTS48RS, ACSR - Full Tension Compression Splice



By Burndy
Catalog # [YTS48RS](#)

Steel Sleeve for Full tension Splice Kit, Length: 9.00 IN, Die Index:
726

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	715.5 Straling Kcmil 795 Drake Kcmil 954 Cardinal Kcmil
---------------------------	---

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - Length Overall	9.00 inch

General

Trade Name	HYSPLICE™
Die Index	726
UPC	781810016282
Material	Aluminum
UPC 12 Digit	781810016282
UPC 14 Digit GTIN	00781810016282

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1350
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)