



YTS48RT481RS, Full Tension Splice Kit for ACSR EHV

By Burndy
Catalog # [YTS48RT481RS](#)



Full Tension Splice Kit for ACSR Conductor EHV

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	900 (45/7) Ruddy Kcmil 954 (45/7) Rail Kcmil
---------------------------	--

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall	741 mm
Dimension - Outside Diameter	1.97 in
Dimension - Length Overall	29.16 in

General

Trade Name	HYSPLICE™
UPC	781810222003
Material	Aluminum
UPC 12 Digit	781810222003
UPC 14 Digit GTIN	00781810222003

Logistics

Minimum Pack Quantity	1
Pallet Quantity	140
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)