



YTS49R, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS49R](#)



Aluminum Sleeve, 1033.5 - 1113 Kcmil ACSR, 230 V, 29.02" L, 727 Index, Included in Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	1033.5 (45/7) Ortolan Kcmil 1033.5 (54/7) Curlew Kcmil 1113 (45/7) Bluejay Kcmil
---------------------------	--

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall	737.1 mm
Dimension - Length Overall	29.02 in
	inch

General

Trade Name	HYSPLICE™
Die Index	727
UPC	781810016114
Material	Aluminum
UPC 12 Digit	781810016114
UPC 14 Digit GTIN	00781810016114

Logistics

Minimum Pack Quantity	1
Pallet Quantity	105
Carton Quantity	3

Product Assets

[Catalog \[English\]](#)