



YTS49R48RS, Full Tension Splice Kit for ACSR

By Burndy
Catalog # [YTS49R48RS](#)



Full Tension Splice Kit for ACSR Conductor

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	1033.5 (54/7) Curlew kcmil
---------------------------	----------------------------

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	4 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall	737 mm
Dimension - Outside Diameter	1.97 in
Dimension - Length Overall	29.02 in

General

Trade Name	HYSPLICE™
UPC	781810515716
Material	Aluminum
UPC 12 Digit	781810515716
UPC 14 Digit GTIN	00781810515716

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalog \[English\]](#)