



YTS521RS, ACSR - Full Tension Compression Splice



By Burndy
Catalog # [YTS521RS](#)

Steel Sleeve, 2167, 2032.1, 2034.5, 1510.5, 1192.5, 1272, 1351.5, 1431
kcmil ACSR, 230 V, 9.00" L, 726 Index, Included in Full Tension
Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	1192.5 (45/7) Bunting Kcmil 1192.5 (54/7) Grackle Kcmil 1351.5 (45/7) Dipper Kcmil 1431 (45/7) Bobolink Kcmil 1510.5 (45/7) Nuthatch Kcmil
---------------------------	--

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall mm	228.6
Dimension - B Length inch	4.00
Dimension - Length Overall inch	9.00

General

Trade Name	HYSPLICE™
Die Index	726
UPC	781810034002
Material	Aluminum
UPC 12 Digit	781810034002
UPC 14 Digit GTIN	00781810034002

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1350
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)