



YTS52R521RS, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS52R521RS](#)



Full Tension Splice Kit for ACSR Conductor

Specifications

Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	1192.5 (45/7) Bunting Kcmil 1351.5 (45/7) Dipper Kcmil 1431 (45/7) Bobolink Kcmil
---------------------------	---

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall mm	1075 mm
Dimension - Outside Diameter inch	2.25 in
Dimension - Length Overall inch	42.33 in

General

Trade Name	HYSPLICE™
UPC	781810485477
Material	Aluminum
UPC 12 Digit	781810485477
UPC 14 Digit GTIN	00781810485477

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)