



YTS52RT59RSHT, Full Tension ACSS EHV Splice Kit

By Burndy
Catalog # [YTS52RT59RSHT](#)



Full Tension ACSS EHV Splice Kits, YTS52RTHT Aluminium Sleeve (Qty. 1), YTS59RS Steel Sleeve (Qty. 1), 1272 (54/19) kcmil-1351.5 (54/19) kcmil

Application

For ACSS Conductor, Corona free operation up to 550 KV

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	Aluminum
Conductor - ACSS Str Size Range	1272 (54/19) kcmil-1351.5 (54/19) kcmil
Conductor - ACSS Str Size	1272 (54/19) kcmil 1351.5 (42/7) kcmil 1351.5 (45/7) kcmil 1351.5 (48/7) kcmil 1351.5 (54/19) kcmil

Configuration

Connector Type	Splice
----------------	--------

Current

Voltage - Maximum	550 kV
-------------------	--------

Dimensions

Dimension - B Length inch	4.07 in
Dimension - Outside Diameter inch	2.25 in
Dimension - Length Overall inch	50.33 in

General

Trade Name	HYSPLICE™
Die Index	728 726
Die Type	L728 for Aluminium Sleeve, L726 Steel Sleeve
UPC	781810515815
Material	Aluminum
UPC 12 Digit	781810515815
UPC 14 Digit GTIN	00781810515815

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)