



YTS549RT549RS, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS549RT549RS](#)



Full Tension Splice Kit for ACSR Conductor EHV

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	UI
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	1590 (45/7) Lapwing kcmil
Conductor - ACSR Str Size Range	1590 (45/7) Lapwing kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	867 mm
Dimension - Outside Diameter	2.50 in
Dimension - Length Overall	34.13 in

General

Trade Name	HYSPLICE™
UPC	781810222102
Material	Aluminum
UPC 12 Digit	781810222102
UPC 14 Digit GTIN	00781810222102

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)