



YTS55AR, Aluminum Full Tension Splice for ACAR

By Burndy
Catalog # [YTS55AR](#)



Aluminum Tube Full Tension HYSPLICE™ for ACAR, 1534 Kcmil, 728 Index

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size	1534 (42-19) Kcmil
---------------------------	--------------------

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	643 mm
------------------------------	--------

Dimension - Length Overall	25.30 in
----------------------------	----------

General

Trade Name	HYSPLICE™
Die Index	728
UPC	781810175880
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810175880
UPC 14 Digit GTIN	00781810175880

Logistics

Minimum Pack Quantity	1
Pallet Quantity	280
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)