



YTS59RT59RS, Full Tension Splice Kit for ACSR EHV

By Burndy
Catalog # [YTS59RT59RS](#)



Full Tension Splice Kit for ACSR Conductor EHV

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	2156 (84/19) Bluebird kcmil
---------------------------	-----------------------------

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall mm	1090 mm
---------------------------------	---------

Dimension - Outside Diameter inch	2.50 in
Dimension - Length Overall inch	42.91 in

General

Trade Name	HYSPLICE™
UPC	781810238912
Material	Aluminum
UPC 12 Digit	781810238912
UPC 14 Digit GTIN	00781810238912

Logistics

Minimum Pack Quantity	1
Pallet Quantity	120
Carton Quantity	2

Product Assets

[Catalog \[English\]](#)