



YTU25R25R, 1-piece Heavy-Wall Aluminum Tap Connector

By Burndy
Catalog # [YTU25R25R](#)



1-piece heavy wall AL compression tap connector for secondary service drop and transformer tap to primary or secondary, 4-7/8 IN L

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run	80 kcmil
Conductor - AL Str Run	1/0 AWG
Conductor - AL Str Tap	1/0 AWG
Conductor - Copper Str Tap	1/0 AWG(7,19,12 STR)
Conductor - ACSR Str Run	80 (8/1) Grouse kcmil
Conductor - ACSR Str Tap	80 (8/1) Grouse kcmil

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	61 mm
Dimension - Height inch	2.40 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	124 mm
Dimension - B Length inch	0.82 in
Dimension - Length Overall inch	4.875 in

General

Plated	N
Die Index Run Side	C
UPC	781810155158
Die Index Tap Side	BG
Prefilled Oxide Inhibitor	Y
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810155158
UPC 14 Digit GTIN	00781810155158

Logistics

Minimum Pack Quantity	6
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)