



YTU25R2R, Aluminum T-Tap Connector

By Burndy
Catalog # [YTU25R2R](#)



Al Compression T-Tap Connector, 1/0 AWG ACSR/Al/Cu(Run), #2 Str ACSR/Al/Cu(Tap)

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run	80 kcmil
Conductor - AL Str Run	1/0 AWG
Conductor - AL Str Tap	2 AWG STR
Conductor - Copper Str Tap	2 AWG(7,8 STR)
Conductor - ACSR Str Run	1/0 AWG
Conductor - ACSR Str Tap	2 AWG(6-1,7-1 STR)

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	61 mm
Dimension - Height inch	2.40 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	123 mm
Dimension - B Length inch	0.82 in
Dimension - Length Overall inch	4.84 in

General

Plated	N
UPC	781810124642
Prefilled Oxide Inhibitor	Y
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810124642
UPC 14 Digit GTIN	00781810124642

Logistics

Minimum Pack Quantity	6
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)