



YTU27R27R, 1-piece Heavy-Wall Aluminum Tap Connector

By Burndy
Catalog # [YTU27R27R](#)



1-piece heavy wall AL compression tap connector for secondary service drop and transformer tap to primary or secondary, 3-3/8 IN Height

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run	3/0 AWG
Conductor - AL Str Run	3/0 AWG
Conductor - AL Str Tap	3/0 AWG
Conductor - Copper Str Tap	3/0 AWG
Conductor - ACSR Str Run	3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Tap	3/0 (6/1) Pigeon AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	84 mm
Dimension - Height inch	3.32 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	178 mm
Dimension - B Length inch	1.88 in
Dimension - Length Overall inch	7 in

General

Plated	N
Die Index Run Side	L
UPC	781810155455
Die Index Tap Side	L
Prefilled Oxide Inhibitor	Y
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810155455
UPC 14 Digit GTIN	00781810155455

Logistics

Minimum Pack Quantity	2
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)