



YTU28R25R, Aluminum T-Tap Connector

By Burndy
Catalog # [YTU28R25R](#)



Al Compression T-Tap Connector, 4/0 AWG ACSR/Al/Cu(Run),
1/0 AWG ACSR/Al/Cu(Tap)

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run	4/0 AWG
Conductor - AL Str Run	4/0 AWG
Conductor - AL Str Tap	1/0 AWG(7,19 STR)
Conductor - Copper Str Tap	1/0 AWG(7,19,12 STR)
Conductor - ACSR Str Run	4/0 AWG
Conductor - ACSR Str Tap	1/0 AWG(6-1 STR)

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	91 mm
Dimension - Height inch	3.59 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	137 mm
mm	
Dimension - B Length inch	2.09 in
Dimension - Length Overall	5.38 in
inch	

General

Plated	N
UPC	781810076989
Prefilled Oxide Inhibitor	Y
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810076989
UPC 14 Digit GTIN	00781810076989

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)