



Z2929, Copper - Compression Cone (Mole)

By Burndy
Catalog # [Z2929](#)

Split Cone, Tubing Brass, 250 kcmil, 0.91" L, 0.78" - 0.66" Dia.

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	250 kcmil
Conductor - Copper Str Size	250 kcmil

Configuration

Connector Type	Cone
----------------	------

Dimensions

Length	0.91 in
--------	---------

Dimension - Cross Flats inch	0.94 in
Dimension - Length Overall inch	0.91

General

Plated	Y
UPC	781810017418
Material	Brass
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810017418
UPC 14 Digit GTIN	00781810017418

Logistics

Minimum Pack Quantity	1
Pallet Quantity	48000
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)