



Z29NR, Copper - Socket And Nut Assembly (Mole)

By Burndy
Catalog # [Z29NR](#)



Socket & Nut Assembly, 250 kcmil, 5/8" - 18 Stud

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	250 kcmil
Range	
Conductor - Copper Str Size	250 kcmil

Configuration

Connector Type	Nut
----------------	-----

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	17/32 in
Package Weight	0.000 lb.
Dimension - Width inch	1.88 in
Package Length	0.000 in
Package Width	0.000 in

Weight	0.76 lb.
Dimension - Cross Flats inch	1.19 in
Dimension - Length Overall inch	3.56

Force Related

Installation Torque	450 lb-in
Recommended in-lb	

General

Plated	Y
UPC	781810017456
Material	Bronze Alloy, Leaded
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810017456
UPC 14 Digit GTIN	00781810017456

Logistics

Minimum Pack Quantity	9
Pallet Quantity	3132
Carton Quantity	9

Product Assets

[Catalog \[English\]](#)