



Z2MLDN420, Copper - Multiple Outlet Connector (Mole)

By Burndy
Catalog # [Z2MLDN420](#)



MOLE Stud Connector, 2000 Amps Capacity, 4 Outlets, #6 Str - 600 kcmil, 1-1/2" Stud Dia.

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	6 AWG-600 kcmil
Conductor - Copper Str Size	6 AWG 5 AWG 4 AWG 3 AWG 2 AWG 1 AWG 1/0 2/0 AWG 3/0 AWG 4/0 AWG 250 kcmil 300 kcmil 350 kcmil 400 kcmil 450 kcmil 500 kcmil 550 kcmil 600 kcmil

Configuration

Number Of Outlets	4
Connector Type	Stud Connector

Dimensions

Package Height	0.000 in
Dimension - Height inch	3
Dimension - B Length fraction	2-11/16 in
Package Weight	0.000 lb.
Dimension - Width inch	5.19
Package Length	0.000 in
Package Width	0.000 in
Diameter - Stud	1.5 in
Dimension - B Length inch	2.69 in
Dimension - Width fraction	3 in
Dimension - Threads per inch	12
Dimension - Length Overall inch	11 in

General

Plated	N
Insulation Type	Diatex
UPC	781810017364
Insulation	Y
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810017364
UPC 14 Digit GTIN	00781810017364

Logistics

Minimum Pack Quantity	3
Pallet Quantity	90
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)