

Z2MLDN430, Stud Mole Assembly

By Burndy
Catalog # [Z2MLDN430](#)



STUD MOLE ASSEMBLY

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	6 AWG-600 kcmil
Conductor - Copper Str Size	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil

Configuration

Number Of Outlets	4
Connector Type	Mole

Dimensions

Dimension - B Length fraction	3-1/4 in
Dimension - Width inch	3 in
Dimension - B Length inch	3.25 in
Dimension - Width fraction	3 in
Dimension - Length Overall	12 in

General

Plated	Y
Insulation Type	Diatex
Trade Name	MOLE™
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810496886
Insulation	Y
Material	Mixed
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810496886
UPC 14 Digit GTIN	00781810496886

Logistics

Minimum Pack Quantity	3
Pallet Quantity	270
Carton Quantity	3

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)