



Z34NRB, Copper - Socket And Nut Assembly (Mole)

By Burndy
Catalog # [Z34NRB](#)



Socket & Nut Assembly, 500 kcmil, 7/8" - 14 Stud

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	500 kcmil
Range	
Conductor - Copper Str Size	500 kcmil

Configuration

Connector Type	Nut
----------------	-----

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	11/16 in
Package Weight	0.000 lb.
Dimension - Width inch	2.13 in
Package Length	0.000 in
Package Width	0.000 in

Weight	0.74 lb.
Dimension - Cross Flats inch	1.50 in
Dimension - Length Overall inch	1.5

Force Related

Installation Torque	700 lb-in
Recommended in-lb	

General

Plated	Y
Insulation Type	Rubber
UPC	781810017470
Material	Bronze Alloy, Leaded
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810017470
UPC 14 Digit GTIN	00781810017470

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2088
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)