



Z36NR, Copper - Socket And Nut Assembly (Mole)

By Burndy
Catalog # [Z36NR](#)



BURNDY; SOCKET AND NUT ASSEMBLY; Z-NR; Designed for use with BURNDY MOLEs; RoHS Compatible with Exemption

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	600 kcmil
Conductor - Copper Str Size	600 kcmil

Configuration

Connector Type	Nut
----------------	-----

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	17/32 in
Package Weight	0.000 lb.
Dimension - Width inch	2.13 in
Package Length	0.000 in
Package Width	0.000 in

Weight	1.4 lb.
Dimension - Cross Flats inch	1.50 in
Dimension - Length Overall inch	1.4

Force Related

Installation Torque Recommended in-lb	450 lb-in
---------------------------------------	-----------

General

Plated	Y
UPC	781810138304
Material	Bronze Alloy, Leaded
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810138304
UPC 14 Digit GTIN	00781810138304

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2784
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)