



Z40NRA, Copper - Socket And Nut Assembly (Mole)

By Burndy
Catalog # [Z40NRA](#)



SOCKET AND NUT ASSEMBLY

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	800 kcmil
Conductor - Copper Str Size	800 kcmil

Configuration

Connector Type	Nut
----------------	-----

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	17/32 in
Package Weight	0.000 lb.
Dimension - Width inch	3.83 in
Package Length	0.000 in
Package Width	0.000 in

Weight	2.4 lb.
Dimension - Cross Flats inch	1.81 in
Dimension - Length Overall inch	5.53

Force Related

Installation Torque Recommended in-lb	450 lb-in
---------------------------------------	-----------

General

Plated	Y
Insulation Type	Rubber
UPC	781810081792
Material	Bronze Alloy, Leaded
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810081792
UPC 14 Digit GTIN	00781810081792

Logistics

Minimum Pack Quantity	10
Pallet Quantity	1110
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)