



Z4444, Split Z Cone

By Burndy
Catalog # [Z4444](#)



Split Cone, Tubing Brass, 1000 kcmil, 1.75" L, 1.50" - 1.27" Dia.

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	1000 kcmil
Conductor - Copper Str Size	1000 kcmil

Configuration

Connector Type	Cone
----------------	------

Dimensions

Package Height	0.000 in
Length	1.75 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - Cross Flats inch	1.62 in
Dimension - Length Overall inch	1.75
General	
Plated	Y
UPC	781810017432
Material	Brass
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810017432
UPC 14 Digit GTIN	00781810017432

Logistics

Minimum Pack Quantity	1
Pallet Quantity	11600
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)