



ZM1225, Copper - Multiple Outlet Connector (Mole)

By Burndy
Catalog # [ZM1225](#)



Copper Mole, 22 in L, Number of Outlets: 12

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	6 AWG-600 kcmil
Conductor - Copper Str Size	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil

Configuration

Number Of Outlets	12
Connector Type	Mole

Dimensions

Dimension - Pad Width inch	4.5 in
Length	22 in
Dimension - Height inch	4.5
Dimension - Width inch	4.5 in
Dimension - Outside Diameter inch	1.52 in
Dimension - Cross Flats inch	1.62 in
Dimension - Length Overall inch	22 in

General

Plated	Y
Trade Name	MOLE™
UPC	781810017241
Insulation	Y
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810017241
UPC 14 Digit GTIN	00781810017241

Logistics

Minimum Pack Quantity	1
Pallet Quantity	96
Carton Quantity	2

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)