

ZM1230B, Mole Assembly

By Burndy
Catalog # [ZM1230B](#)

MOLE ASSY



Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

- 800 kcmil
- 850 kcmil
- 900 kcmil
- 1000 kcmil

Configuration

Number Of Outlets	12
Connector Type	Mole

Dimensions

Dimension - Pad Width inch	3.38 in
Dimension - Width inch	5 in
Dimension - Length Overall inch	20.44 in

General

UPC	781810122679
Insulation	Y
UPC 12 Digit	781810122679
UPC 14 Digit GTIN	00781810122679

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)

Conductor

Conductor - Copper Str Size Range	2 AWG-1000 kcmil
Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil