

## ZM1425B, Mole Assembly

By Burndy  
Catalog # [ZM1425B](#)

MOLE ASSEMBLY



### Specifications

|                                    |    |
|------------------------------------|----|
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Standards - RoHS Compliance Status | EX |
| Certification - cULus              | No |
| UL Listed                          | No |
| Certification - CSA Approved       | No |

### Conductor

|                                   |                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|-----------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - Copper Str Size Range | 2 AWG-1000 kcmil                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Conductor - Copper Str Size       | <ul style="list-style-type: none"><li>• 2 AWG</li><li>• 1 AWG</li><li>• 1/0</li><li>• 2/0 AWG</li><li>• 3/0 AWG</li><li>• 4/0 AWG</li><li>• 250 kcmil</li><li>• 300 kcmil</li><li>• 350 kcmil</li><li>• 400 kcmil</li><li>• 450 kcmil</li><li>• 500 kcmil</li><li>• 550 kcmil</li><li>• 600 kcmil</li><li>• 700 kcmil</li><li>• 750 kcmil</li><li>• 800 kcmil</li><li>• 850 kcmil</li><li>• 900 kcmil</li><li>• 1000 kcmil</li></ul> |

### Configuration

|                   |      |
|-------------------|------|
| Number Of Outlets | 14   |
| Connector Type    | Mole |

### Dimensions

|                                   |         |
|-----------------------------------|---------|
| Dimension - Pad Width inch        | 4.5 in  |
| Length                            | 25.5 in |
| Dimension - Height inch           | 4.5     |
| Dimension - Width inch            | 4.5 in  |
| Dimension - Outside Diameter inch | 1.89 in |
| Dimension - Cross Flats inch      | 1.62 in |
| Dimension - Length Overall inch   | 25.5 in |

### General

|                   |                |
|-------------------|----------------|
| Plated            | Y              |
| UPC               | 781810158302   |
| Insulation        | Y              |
| Material          | Copper         |
| Plating Type      | Tin            |
| UPC 12 Digit      | 781810158302   |
| UPC 14 Digit GTIN | 00781810158302 |

### Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 2   |
| Pallet Quantity       | 144 |
| Carton Quantity       | 2   |

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)