



ZM1625, Copper - Multiple Outlet Connector (Mole)

By Burndy
Catalog # [ZM1625](#)

Copper Mole, 29 in L, Number of Outlets: 16



Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	6 AWG-600 kcmil
Conductor - Copper Str Size	6 AWG 5 AWG 4 AWG 3 AWG 2 AWG 1 AWG 1/0 2/0 AWG 3/0 AWG 4/0 AWG 250 kcmil 300 kcmil 350 kcmil 400 kcmil 450 kcmil 500 kcmil 550 kcmil 600 kcmil

Configuration

Number Of Outlets	16
Connector Type	Mole

Dimensions

Dimension - Pad Width inch	4.5 in
Length	29 in
Dimension - Height inch	4.5
Dimension - Width inch	4.5 in
Dimension - Outside Diameter inch	1.52 in
Dimension - Cross Flats inch	1.62 in
Dimension - Length Overall inch	29 in

General

Plated	Y
Trade Name	MOLE™
UPC	781810017302
Insulation	Y
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810017302
UPC 14 Digit GTIN	00781810017302

Logistics

Minimum Pack Quantity	1
Pallet Quantity	35
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)