

ZM1625B, Z Mole

By Burndy
Catalog # [ZM1625B](#)

Z MOLE



Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	2 AWG-1000 kcmil
Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil • 850 kcmil • 900 kcmil • 1000 kcmil

Configuration

Number Of Outlets	16
Connector Type	Mole

Dimensions

Dimension - Pad Width inch	4.5 in
Length	29 in
Dimension - Height inch	4.5
Dimension - Width inch	4.5 in
Dimension - Outside Diameter inch	1.89 in
Dimension - Length Overall inch	29 in

General

Plated	Y
Trade Name	MOLE™
UPC	781810327906
Insulation	Y
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810327906
UPC 14 Digit GTIN	00781810327906

Logistics

Minimum Pack Quantity	1
Pallet Quantity	35
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)