

ZM1630, Copper - Multiple Outlet Connector (Mole)

By Burndy
Catalog # [ZM1630](#)

MOLE ASSY



Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

- 550 kcmil
- 600 kcmil

Conductor

Conductor - Copper Str Size Range	6 AWG-600 kcmil
Conductor - Copper Str Size	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil

Configuration

Number Of Outlets	16
Connector Type	Mole

Dimensions

Dimension - Pad Width inch	3.38 in
Dimension - Width inch	5 in
Dimension - Length Overall inch	27.19 in

General

UPC	781810140321
Insulation	Y
UPC 12 Digit	781810140321
UPC 14 Digit GTIN	00781810140321

Logistics

Minimum Pack Quantity	1
Pallet Quantity	35
Carton Quantity	1

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)