

ZM630B, Mole Assembly

By Burndy  
Catalog # [ZM630B](#)

MOLE ASSY



Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | EX |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

- 900 kcmil
- 1000 kcmil

Conductor

|                                   |                                                                                                                                                                                                                                                                                                                                                                                             |
|-----------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - Copper Str Size Range | 2 AWG-1000 kcmil                                                                                                                                                                                                                                                                                                                                                                            |
| Conductor - Copper Str Size       | <ul style="list-style-type: none"><li>• 2 AWG</li><li>• 1 AWG</li><li>• 1/0</li><li>• 2/0 AWG</li><li>• 3/0 AWG</li><li>• 4/0 AWG</li><li>• 250 kcmil</li><li>• 300 kcmil</li><li>• 350 kcmil</li><li>• 400 kcmil</li><li>• 450 kcmil</li><li>• 500 kcmil</li><li>• 550 kcmil</li><li>• 600 kcmil</li><li>• 700 kcmil</li><li>• 750 kcmil</li><li>• 800 kcmil</li><li>• 850 kcmil</li></ul> |

Configuration

|                   |      |
|-------------------|------|
| Number Of Outlets | 6    |
| Connector Type    | Mole |

Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - Pad Width inch      | 3.38 in  |
| Dimension - Width inch          | 5 in     |
| Dimension - Length Overall inch | 10.31 in |

General

|                   |                |
|-------------------|----------------|
| Insulation Type   | Diatex         |
| UPC               | 781810217863   |
| Insulation        | Y              |
| Material          | Diatex         |
| UPC 12 Digit      | 781810217863   |
| UPC 14 Digit GTIN | 00781810217863 |

Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 1   |
| Pallet Quantity       | 546 |
| Carton Quantity       | 2   |

Product Assets

- [Catalog \[English\]](#)  
[Installation Manual \[English\]](#)