



ZM825B, Copper - Multiple Outlet Connector (Mole)

By Burndy
Catalog # [ZM825B](#)



MOLE ASSY

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	2 AWG-1000 kcmil
Conductor - Copper Str Size	2 AWG 1 AWG 1/0 2/0 AWG 3/0 AWG 4/0 AWG 250 kcmil 300 kcmil 350 kcmil 400 kcmil 450 kcmil 500 kcmil 550 kcmil 600 kcmil 700 kcmil 750 kcmil 800 kcmil 850 kcmil 900 kcmil 1000 kcmil

Configuration

Number Of Outlets	8
Connector Type	Mole

Dimensions

Dimension - Pad Width inch	4.5 in
Length	15 in
Dimension - Height inch	4.5
Dimension - Width inch	4.5 in
Dimension - Outside Diameter inch	1.89 in
Dimension - Cross Flats inch	1.62 in
Dimension - Length Overall inch	15 in

General

Plated	Y
Trade Name	MOLE™
UPC	781810178003
Insulation	Y
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810178003
UPC 14 Digit GTIN	00781810178003

Logistics

Minimum Pack Quantity	1
Pallet Quantity	180
Carton Quantity	2

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)