

ZMS29, Copper - Coupler (Mole)

By Burndy
Catalog # [ZMS29](#)

MOLE Coupler, 1200 Amp Capacity, #6 Str - 600 kcmil, 4-21/32"
L



Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	6 AWG-600 kcmil
Conductor - Copper Str Size	6 AWG 5 AWG 4 AWG 3 AWG 2 AWG 1 AWG 1/0 2/0 AWG 3/0 AWG 4/0 AWG 250 kcmil 300 kcmil 350 kcmil 400 kcmil 450 kcmil 500 kcmil 550 kcmil 600 kcmil

Configuration

Number Of Outlets	2
Connector Type	Couplers

Dimensions

Package Height	0.000 in
Dimension - Body Width inch	1.19 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Nut Width inch	1.38 in
Dimension - Cross Flats inch	1.19 in
Dimension - Width fraction	1-3/16 in
Dimension - Length Overall inch	4.66 in

General

Plated	Y
Trade Name	MOLE™
UPC	781810017371
Material	Bronze Alloy, Leaded
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810017371
UPC 14 Digit GTIN	00781810017371

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1392
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)