

ZMS34, Mole Coupler

By Burndy
Catalog # [ZMS34](#)

MOLE Coupler, 1600 Amp Capacity, #2 Str - 1000 kcmil, 5-7/32"
L



Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

- 1000 kcmil

Conductor

Conductor - Copper Str Size Range	2 AWG-1000 kcmil
Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil • 850 kcmil • 900 kcmil

Configuration

Number Of Outlets	2
Connector Type	Couplers

Dimensions

Dimension - Body Width inch	5.5 in
Dimension - Nut Width inch	1.75 in
Dimension - Cross Flats inch	5.5 in
Dimension - Width fraction	1-1/2 in
Dimension - Length Overall inch	5.22 in

General

Plated	Y
Trade Name	MOLE™
UPC	781810017265
Material	Bronze Alloy, Leaded
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810017265
UPC 14 Digit GTIN	00781810017265

Logistics

Minimum Pack Quantity	2
Pallet Quantity	928
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)