



ZMT915, Copper - Multiple Outlet Connector (Mole)

By Burndy
Catalog # [ZMT915](#)



MOLE Assembly, 1500 Amps Capacity, #6 Str - 600 kcmil

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	6 AWG-600 kcmil
Conductor - Copper Str Size	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil

Configuration

Number Of Outlets	9
Connector Type	Mole

Dimensions

Dimension - Pad Width inch	3 in
Dimension - Width inch	4.13 in
Dimension - Length Overall inch	14 in

General

Plated	Y
Insulation Type	Diatex
Trade Name	MOLE™
UPC	781810017340
Material	Mixed
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810017340
UPC 14 Digit GTIN	00781810017340

Logistics

Minimum Pack Quantity	1
Pallet Quantity	240
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)