

# Eaton 3.6WDFHO80

Catalog Number: 3.6WDFHO80

Eaton Bussmann series medium voltage motor fuse, 80 A, 3.6 kV, 51 x 254 mm, Non Indicating

## General specifications

Product Name	Catalog Number
Eaton Bussmann series medium voltage motor fuse	3.6WDFHO80
	UPC
	051712616782
EAN	Product Length/Depth
5027590474269	254 mm
Product Height	Product Width
51 mm	51 mm
Product Weight	Warranty
1460 g	Not Applicable
Compliances	
BS 2692-1	

## Product specifications

### Interrupt rating

50 kAIC

### Standard

British Standard

### Release characteristic

Other

### Amperage Rating

80 A

### Fuse type

WDFH

### Rated frequency - min

50 Hz

### Fuse size

51 x 254 mm

### With striker

Yes

### Voltage rating

3.6 kV

### Fuse indicator

Non Indicating

### Rated frequency - max

50 Hz

### Performance Cat According To IEC 60282-1

Back-up

### Construction size

51 x 254 mm

### Utilization category

Other

### Watt losses

31 W

### Barrels

1

### Resistance

3.52 ohms

### Type

## Resources

### Catalogs

[3.6WDFHO80~3-6WDFHO80~3.6KV 80Amp 2 'O' MOTORSTART FUSE](#)

[Bussmann series complete full line catalog no. 1007](#)

### Specifications and datasheets

[Eaton Specification Sheet - 3.6WDFHO80](#)

fuse

Fuse diameter

51 mm

Fuse shape

Cylindrical, offset bolted tags

Used with

A3354710 Nickel-plated copper fuse clip

Breaking capacity

50 A

Class

Class back-up

Product application

Motor protection

Application

Motor protection

Installation technique

Air

Voltage type

AC

Packaging type

Standard



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)