

Eaton 40FE

Catalog Number: 40FE

Eaton Bussmann series high speed British standard fuse, Single barrel, 40A, 690 VAC/500 VDC (IEC), 700 VAC/500 VDC (UL), Class aR, Breaking capacity 200 kA RMS Sym., 50 kA DC at 500 VDC

General specifications

Product Name	Catalog Number
Eaton Bussmann series high speed British standard fuse	40FE
	UPC
	051712834995
EAN	Product Length/Depth
5027590480109	76 mm
Product Height	Product Width
20 mm	20 mm
Product Weight	Warranty
40.6 g	Not Applicable
Compliances	Certifications
CE Marked	IEC Rated
RoHS Compliant	UL Recognized
	Designed and tested to BS88 part 4
	IEC 60269-4



Electrical data

Amperage Rating

40 A

Voltage rating

690 V (IEC), 700 V (UL)

Rated voltage AC

690 V

Rated voltage DC

500 V

Interrupt rating

200 kA RMS Sym, 50 kA at 500 Vdc

Class

Class aR

Pre arc (I2T)

52

Clearing (I2T)

180 at 415 V, 300 at 660 V

Watt losses

9 W

Product specifications

Application

Semiconductor, DC Common bus, DC drives, power converters/rectifiers

Fuse indicator

None

Compatible Trip indicator/Microswitch

Suitable for

EC-600 Trip indicator kit (indicator + clips)

TI700 Fuse indicator

MAI Microswitch/adaptor

MBI Microswitch/adaptor

Resources

Brochures

[eaton-bussmann-series-bs88-high-speed-fuses-product-aid-pa135003en-us.pdf](#)

Catalogs

[IEC high speed fuse links](#)

[Bussmann series complete full line catalog no. 1007](#)

Certification reports

[DA-DC-00004685](#)

[DA-DC-00004682](#)

Compliance information

[UKCA Low voltage fuse-links *AET,*AEET,*AFEE etc](#)

Specifications and datasheets

[Eaton Specification Sheet - 40FE](#)

Technical data sheets

[720024 CT, ET, FE, EET, FEE, FM, FMM, MT, MMT fuses](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)