

# Eaton DMM-B-44/100

Catalog Number: DMM-B-44/100

Eaton Bussmann series DMM-B fuse, Fast acting fuse, Multimeters only, 0.44 A, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 1000 Vac/dc, Standard, 1000 V, 1000 Vdc

## General specifications



Product Name	Catalog Number
Eaton Bussmann series DMM-B fuse	DMM-B-44/100
UPC	EAN
051712550550	5027590059572
Product Length/Depth	Product Height
0.46 in	1.5 in
Product Width	Product Weight
0.46 in	0.15 lb
Warranty	Compliances
Not Applicable	CE Marked

## Product specifications

[Fuse indicator](#)

Non-indicating

[Special features](#)

Non current limiting

[Interrupt rating](#)

10 kAIC at 1000 Vac/dc

[Type](#)

Fast acting fuse

[Connection](#)

Ferrule end x ferrule end

[Voltage rating](#)

1000 Vac, 1000 Vdc

[Application](#)

Multimeters only

[Amperage Rating](#)

0.44A

[Packaging type](#)

Standard

## Resources

[Catalogs](#)

Bussmann series complete full line catalog no. 1007

[Specifications and datasheets](#)

Eaton Specification Sheet - DMM-B-44/100

[Technical data sheets](#)

DMM-B-44/100~DMM-B-44-100~DMM FUSE - BUSSMANN

Bussmann series DMM digital multi-meter fuse data sheet No.1047



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)