

Eaton ED250

Catalog Number: ED250

Eaton Bussmann series low voltage British standard fuse, Fuse-link, LV, 250 A, AC 415 V, BS88/B3, BS88/B4, 31 x 136 mm, gL/gG, BS

General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage British standard fuse	ED250
	UPC
	051712839709
EAN	Product Length/Depth
5027590018944	136 mm
Product Height	Product Width
31 mm	31 mm
Product Weight	Warranty
168 g	Not Applicable
Compliances	
RoHS Compliant	

Electrical rating

Amperage Rating

250 A

Breaking capacity

80 kA

Interrupt rating

80 kAIC

Rated switching capacity

80 kA

Voltage rating

415 V

Voltage type

AC

Physical details

Color

None

Fuse type

ED

General information

Class

Class gG/gL

Connection

111 mm fixing centre

Construction size

Other

Fitted with:

Centre bolted tags

Fuse indicator

None

Fuse shape

Center bolted tags

Fuse size

BS88/B3

BS88/B4

Insulated metal gripping lugs (IMGL)

No

Utilization category

gL/gG (cable protection/equipment protection)

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

Compliance information

[UKCA DD and ED low voltage fuse-links](#)

[CE DD and ED low voltage fuse-links](#)

Specifications and datasheets

[Eaton Specification Sheet - ED250](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)