

Eaton FNQ-R-2-8/10

Catalog Number: FNQ-R-2-8/10

Eaton Bussmann series FNQ-R fuse, 2.8 A, Class CC, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAIC, Melamine tube, Standard, 600 V

General specifications

Product Name	Catalog Number
Eaton Bussmann series FNQ-R fuse	FNQ-R-2-8/10
UPC	EAN
051712496988	5704057045216
Product Length/Depth	Product Height
0.41 in	1.5 in
Product Width	Product Weight
0.41 in	0.15 lb
Warranty	Compliances
Not Applicable	CE Marked
	RoHS Compliant



Electrical Ratings

Amperage Rating

2.8A

Voltage rating

600 V

General Information

Application

Line protection, small control transformers, industrial control, branch circuits

Connection

Ferrule end x ferrule end

Special features

Rejection style

Physical Details

Type

Current-limiting high inrush time-delay fuse

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - FNQ-R-2-8/10](#)

Technical data sheets

[FNQ-R-2-8/10~FNQ-R-2-8-10~CLASS CC TIME DELAY](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)