

Eaton FNQ-R-25

Catalog Number: FNQ-R-25

Eaton Bussmann series FNQ-R fuse, 25 A, Class CC, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAIC, Melamine tube, Standard, 600 V

General specifications

Product Name	Catalog Number
Eaton Bussmann series FNQ-R fuse	FNQ-R-25
UPC	EAN
051712497138	5027590449724
Product Length/Depth	Product Height
0.41 in	1.5 in
Product Width	Product Weight
0.41 in	0.15 lb
Warranty	Compliances
Not Applicable	CE Marked
	RoHS Compliant



Electrical Ratings

Amperage Rating

25 A

Voltage rating

600 V

General Information

Application

Line protection, small control transformers, industrial control, branch circuits

Connection

Ferrule end x ferrule end

Special features

Rejection style

Physical Details

Type

Current-limiting high inrush time-delay fuse

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - FNQ-R-25

Technical data sheets

FNQ-R-25~CLASS CC TIME DELAY REJECTION FUSE

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia