

Eaton FRN-R-400

Catalog Number: FRN-R-400

Eaton Bussmann series FRN-R fuse, 400 A, Dual, Class RK5, Non-indicating, Blade end x blade end, 10 sec at 500%, 20 kAIC at 125 Vdc|200 kAIC at 250 V, Standard, 250 V, 125 Vdc

General specifications

Product Name	Catalog Number
Eaton Bussmann series FRN-R fuse	FRN-R-400
UPC	EAN
051712507530	5027590060813
Product Length/Depth	Product Height
8.63 in	2.06 in
Product Width	Product Weight
2.06 in	1.6 lb
Warranty	Compliances
Not Applicable	CE Marked

Electrical rating

Amperage Rating

400 A

Interrupt rating

200 kAIC at 250 Vac

20 kAIC at 125 Vdc

Response time

10 sec at 500%

Voltage rating

250 Vac, 125 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Connection

Blade end x blade end

Fuse indicator

Non-indicating

Special features

Finger safe

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - FRN-R-400](#)

Technical data sheets

[FRN-R-400~FUSETRON DUAL-ELEMENT CLASS RK5](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)