

Eaton FRS-R-60

Catalog Number: FRS-R-60

Eaton Bussmann series FRS-R fuse, 60 A, Dual, Class RK5, Non-indicating Ferrule end x ferrule end, 10 sec at 500%, 200 kAIC at 600 V|20 kAIC at 250 Vdc, Standard, 600 V, 250 Vdc

General specifications



Product Name	Catalog Number
Eaton Bussmann series FRS-R fuse	FRS-R-60
UPC	Product Length/Depth
051712508391	13.38 in
Product Height	Product Width
2.88 in	2.88 in
Product Weight	Warranty
3.6 lb	Not Applicable
Compliances	
CE Marked	

Electrical rating

Amperage Rating

60 A

Interrupt rating

200 kAIC at 600 Vac

20 kAIC at 250 Vdc

Response time

10 sec at 500%

Voltage rating

600 Vac, 250 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Resources

Catalogs

Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - FRS-R-60

Technical data sheets

FRS-R-60~FUSETRON DUAL ELEMENT FUSE CLASS RK5

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)