

Eaton FWA-50A21F

Catalog Number: FWA-50A21F

Eaton Bussmann series FWA high speed fuse, 500 Vac/dc (35-800A only), 50A, 100 kAIC, Non Indicating, High speed fuse, Ferrule end X ferrule end

General specifications

Product Name	Catalog Number
Eaton Bussmann series high speed cylindrical fuse	FWA-50A21F
	UPC
	051712795289
EAN	Product Length/Depth
5027590499286	62 mm
Product Height	Product Width
47 mm	110 mm
Product Weight	Warranty
56.2 g	Not Applicable
Compliances	Certifications
CE Marked	CSA Certified
RoHS Compliant	UL Recognized



Product specifications

Fuse indicator

Other

Interrupt rating

100 kAIC

Construction size

Other

Clearing (I2T)

1600 at 150 V

Connection

Ferrule end x ferrule end

Material

Ceramic

Release characteristic

Other

Amperage Rating

50 A

Frequency rating - max

62 Hz

Utilization category

aR (accompanied semiconductor protection)

Watt losses

7.3 W

Fuse type

FWA-A21F

Type

High speed fuse

Fuse shape

Cylindrical

Breaking capacity

200 kA

Fuse size

21 x 51 mm

Frequency rating - min

45 Hz

Class

Resources

Catalogs

IEC high speed fuse links

Bussmann series complete full line catalog no. 1007

Specifications and datasheets

Eaton Specification Sheet - FWA-50A21F

Technical data sheets

720003 FWA

Class aR

Pre arc (I2T)

170

Voltage rating

150 V

Application

Semiconductor, DC Common bus, DC drives, Power converters/rectifiers

Voltage type

AC/DC

Packaging type

Standard



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)